



**OT600U30C**  
 600VAC 600A 3-Pole  
 Manual Transfer Switch  
 Rotary operated, 3-Pos.,  
 center OFF, open transition  
 Open Type Switch  
 UL File #101914  
 CSA Certified, File #58077

KA	Fuse/A	Fuse class	UL, T or L
100	800		J, T or L
100	600		RKS
30			Circuit Breaker

3-phase HP Ratings  
 VAC 208 240 480 600  
 HP - 200 450 500

Operating Handle  
 OXB12312E011 - Type 1, 3R, 4, 4A, 12  
 OXB173112E011 - Type 1, 3R, 4, 4A, 12  
 Ref. drawing D 2301 8001-002 for  
 pistol grip handle dimensions and  
 installation details.

Terminal Lug Kits  
 O2XA-800 - 6 lugs  
 O2YA-800/9 - 9 lugs,  
 for use with OTZC busbar kit

Operating Shift - Max. encl. depth  
 OXE12X220 - 14.20 in.  
 OXE12X280 - 16.50 in.  
 OXE12X325 - 18.30 in.  
 OXE12X395 - 21.10 in.  
 OXE12X465 - 23.80 in.  
 OXE12X625 - 30.10 in.

Auxiliary Contacts  
 OA1G10 - In.c.  
 OA3S01 - In.c.

Accessories:  
 Operating Handle  
 OXB12312E011 - Type 1, 3R, 4, 4A, 12  
 OXB173112E011 - Type 1, 3R, 4, 4A, 12  
 Ref. drawing D 2301 8001-002 for  
 pistol grip handle dimensions and  
 installation details.

Terminal Lugs  
 Wire Range:  
 (2) #2 AWG - 600kcmil  
 AL70U, UL Listed

Bridging busbar kit:  
 OTZC33  
 (3 pos., for common  
 hood connection)

REV. LET.	REVISIONS	DATE	REV OR APPD BY	THIS DRAWING IS THE PROPERTY OF ABB Inc. AND CONTAINS PROPRIETARY AND CONFIDENTIAL INFORMATION WHICH MUST NOT BE OR DISCLOSED OTHER THAN EXPRESSLY AUTHORIZED BY ABB Inc.	ABB Inc.	DATE 10-12-07	REV. A	TITLE OT600U30C Transfer Switch
						DRAWN JWD	SIZE A	DRAWING NUMBER D 2501 8060-033
						PROJECT NO.		
						SHEET 1 OF 1		