





DRAWING NUMBER
D 2501 8003-003



OT30-100F3
600VAC 30-100A 3-POLE
OPEN TYPE SWITCH
ROTARY OPERATED,
Open Type Switch
UL File #101914
CSA Certified, File #58077

OT60-100F3
SHORT CIRCUIT RATING AT 600VAC

KA	Fuse/A	Fuse class
50	150	J
50	150	T

OT30
SHORT CIRCUIT RATING AT 600VAC

KA	Fuse/A	Fuse class
50	60	J
50	60	T

ACCESSORIES:
OPERATING HANDLE
OHB65J6 - TYPE 1, 3R, 12
OHB65L6 - TYPE 1, 3R, 4, 4X, 12

OPERATING SHAFT - MAX. ENCL. DEPTH
OXP6X150 - 6.7 IN.
OXP6X210 - 7.0 IN.
OXP6X290 - 9.8 IN.
OXP6X360 - 12.9 IN.
OXP6X430 - 15.6 IN.
OXP6X700 - 18.3 IN.

AUXILIARY CONTACTS
OA1G10 - 1N.O.
OA1G01 - 1N.C.

3-PHASE HP RATINGS

VAC	240	480	600
HP	40	75	100

REV. LET.	REVISIONS	DATE	REV OR APPD BY

DO NOT SCALE DRAWING


SCALE 1/2" DIMENSIONS ARE IN INCHES

Material: _____

Finish: _____

STANDARD TOLERANCES
2 PL DEC. ±.030 3 PL DEC. ±.030 ANGLES ±1°

THIS DRAWING IS THE PROPERTY OF ABB Inc. AND CONTAINS PROPRIETARY AND CONFIDENTIAL INFORMATION WHICH MUST NOT BE OR DISCLOSED OTHER THAN EXPRESSED BY ABB Inc.



DATE 11/10/08
DRAWN TSP
CHK'D _____
APPRID _____
SHEET 1 OF 1

REV. **A** TITLE
OT30F3-OT100F3 DISCONNECT SWITCH

SIZE **A** DRAWING NUMBER **D 2501 8003-003**

PART