



TYPICAL COMPONENTS

AMP	Jump	HP	MODEL	BFT STR	SFT MOTOR	OL	OOT	MOSES
MIN	Max 1.	480V						
60	65	125	T20L1-G	PST175-300-10	A.050-30-115A	5000 LMD	T6.30Psf 1	55 K4050
75	80	140	T40L1-G	PST175-300-10	A.210-30-115A	5000 LMD	T6.30Psf 1	55 K4400
75	240	200	T40L1-G	PST290-500-10	A.050-30-115A	5000 LMD	T6.30Psf 1	55 K4400
50	302	250	T20L1-G	PST300-500-10	A.050-30-115A	5000 LMD	T6.30Psf 1	55 K5000

NOTES:
TYPICAL COMPONENTS BASED ON 480 V
AND 120 V CONTROL VOLTAGE. FOR
OTHER THAN CLASS TO LINE START OR
MINIMAL LOAD APPL. CONTACT FACTORY.

DRAWING NUMBER
D 2401 1420-050



NOTES:

- 1) PLACE RUN LIGHT ABOVE DEVICE USED TO STOP MOTOR.
- 2) FOR MODELS EQUIPPED WITH HOA AND START-STOP, PLACE STOP TO LEFT OF HOA. PLACE RUN LIGHT ABOVE HOA IF REQUIRED.

FRONT VIEW

SIDE VIEW

SECTION "A"- "A"

REV.	APPD BY	DATE	REV OR APPD BY	DATE	REV.	TITLE
ADD EQUIPMENT TABLE		10/12/04	DO NOT SCALE DRAWING			
REVISED EQUIPMENT LOCATIONS	KBM	9/10/04	SCALE 3/32	DIMENSIONS ARE IN INCHES		
REVISED CB & OL RANGE, ALSO CONNECTION NOTE	KBM	8/9/04	MATERIAL C-S0363610	36.36x12 TYPE 12, 4		
ADD E-BYP LABEL TO DOOR, ADD K6ET-800 TO OL CONNECTION NOTE	KBM	7/9/04	FINISH:			
ADD PANEL MOUNT E-BYP SWITCH	KBM	7/7/04	STANDARD TOLERANCES	ANGLES ±1°		
REVISIONS			2 PL. DEC. ±.030	3 PL. DEC. ±.030		



ABB Inc.

DATE: 2/18/04
DRAWN: KBM
CHK'D:
APP'D:
REV. F
TITLE: PANEL LAYOUT SFT STR
PST175-300, N1,12,4,3R,CB
DRAWING NUMBER: D 2401 1420-050

SHOP