

Molded Case Dimensions & Ratings



Frame	Type	Trip range	H	W	D	Voltage	480 V AC
T1	tmag	15-100A	5.12	3	2.76	600Y	22kA
T2	elec or tmag	4-100A	5.12	3.54	2.76	480	35kA, 65kA
T3	tmag	60-225A	5.9	4.13	2.76	600Y	25kA, 35kA
S3 [Ⓞ]	tmag	15-225A	6.7	4.13	4.07	600	25kA, 50kA, 85kA
T4	elec or tmag	40-250A	8.07	4.13	4.07	600	25kA, 35kA, 65kA, 100kA, 150kA
T5	elec or tmag	120-600A	8.07	5.51	4.07	600	25kA, 35kA, 65kA, 100kA, 150kA
S6	elec or tmag	240-800A	10.55	8.27	4.07	600	50kA, 65kA, 100kA
S7	elec	400-1200A	15.98	8.27	5.45	600	65kA
S8	elec	640-2500A	15.75	15.98	9.25	600	100kA

150U 210 062 E001

[Ⓞ] For special applications only.

RESULTS-DRIVEN POWER CONTROL



Molded Case Quick Reference



Frame Size	ABB	CH	GE	MG	Sq D	Siemens
15-100A	T1 & T2	GD & EHD	TED	NSE	FA	ED
15-150A	S3	FD	TED	NSF150	FA & H	ED
60-225A	T3 & S3	FD	TFK	NSF250	FA	FD6
250A	T4	JD	TFJ	NSF250	KA & J	FD6
400A	T5	KD	TJJ & TJK4	NSJ400	LA	JD6
600A	T5	LD	TJK6	NSJ600	MA	LD6 & MD6
800A	S6	MD	TKM8	CK800	MA & M	LMD6
1200A	S7	MD	TKM12	CK1200	NA & P	ND6
1600A	S8	RD		CM	PA & R	PD6

**RESULTS-DRIVEN
POWER CONTROL**

