


PART NUMBER	LENGTH (IN.)	LENGTH (mm)
OXS6X100	3.94 IN.	100mm
OXS6X105	4.13 IN.	105mm
OXS6X109	4.29 IN.	109mm
OXS6X115	4.53 IN.	115mm
OXS6X117	4.61 IN.	117mm
OXS6X120	4.72 IN.	120mm
OXS6X130	5.12 IN.	130mm
OXS6X150	5.91 IN.	150mm
OXS6X160	6.30 IN.	160mm
OXS6X180	7.09 IN.	180mm
OXS6X203	7.99 IN.	203mm
OXS6X209	8.23 IN.	209mm
OXS6X213	8.39 IN.	213mm
OXS6X237	9.33 IN.	237mm
OXS6X250	9.84 IN.	250mm
OXS6X330	12.99 IN.	330mm
OXS6X455	17.91 IN.	455mm
OXS6X47	1.85 IN.	47mm
OXS6X53	2.09 IN.	53mm
OXS6X57	2.24 IN.	57mm
OXS6X73	2.87 IN.	73mm
OXS6X85	3.35 IN.	85mm
OXS6X95	3.74 IN.	95mm

PART

DO NOT SCALE DRAWING		THIS DRAWING IS THE PROPERTY OF ABB Inc. AND CONTAINS PROPRIETARY AND CONFIDENTIAL INFORMATION WHICH MUST NOT BE DUPLICATED, USED OR DISCLOSED OTHER THAN EXPRESSLY AUTHORIZED BY ABB Inc.		DATE	REV.	TITLE
SCALE	DIMENSIONS			1/21/09	A	OXS6X___ SELECTOR SHAFT DRAWING
N/A	ARE IN INCHES			DRAWN		
Material:				TSP		
Finish:		CHK'D	SIZE	DRAWING NUMBER		
		APPR'D	A	D 2501 8001-008		
STANDARD TOLERANCES		ABB Inc.	SHEET	1 OF 1		
2 PL DEC. ±.030	3 PL DEC. ±.030					